

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267763

Luminaire Tested: P3A17R259735DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R259735DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 963.0 lumens
Efficiency: N/A
Efficacy: 45.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267763

CATALOG NUMBER: P3A17R259735DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267763

CATALOG NUMBER: P3A17R259735DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228863
5°	223398
10°	207032
15°	184382
20°	158447
25°	134693
30°	110878
35°	86384
40°	62145
45°	39446
50°	23334
55°	16057
60°	14736
65°	13698
70°	12310
75°	11184
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 39446 cd/sqm

TEST NUMBER: P1267763

CATALOG NUMBER: P3A17R259735DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	9.8
10°-20°	225.5	23.4
20°-30°	254.8	26.5
30°-40°	201.5	20.9
40°-50°	101.8	10.6
50°-60°	40.8	4.2
60°-70°	26.1	2.7
70°-80°	14.4	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.4	59.6
0°-40°	775.9	80.6
0°-60°	918.4	95.4
0°-90°	963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	963.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1044	
5°	1015	94
15°	812	225
25°	557	255
35°	323	202
45°	127	102
55°	42	41
65°	26	26
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P1267763

CATALOG NUMBER: P3A17R259735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1043.7
1°	1043.7
2°	1040.1
3°	1034.1
4°	1025.7
5°	1014.9
6°	1001.7
7°	986.1
8°	969.4
9°	950.2
10°	929.8
11°	907.0
12°	885.4
13°	860.2
14°	836.2
15°	812.2
17.5°	745.0
20°	679.0
22.5°	616.6
25°	556.7
27.5°	497.9
30°	437.9
32.5°	381.5
35°	322.7
37.5°	268.7
40°	217.1
42.5°	169.2
45°	127.2
47.5°	94.8
50°	68.4
52.5°	51.6
55°	42.0
57.5°	38.4
60°	33.6
62.5°	30.0
65°	26.4
67.5°	22.8
70°	19.2
72.5°	16.8
75°	13.2
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2



TEST NUMBER: P1267763

CATALOG NUMBER: P3A17R259735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)