

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266006

Luminaire Tested: P3A20R709730D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1266006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R709730D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1896.0 lumens  
Efficiency: N/A  
Efficacy: 65.8 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266006

CATALOG NUMBER: P3A20R709730D010 E3CD1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1266006

CATALOG NUMBER: P3A20R709730D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  |  | 88  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 77  | 94  | 86  | 81  | 76  | 84  | 79  | 75  |  | 82  | 78  | 75  |  | 80  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  |
| 6   | 85  | 75  | 69  | 64  | 83  | 75  | 69  | 64  | 73  | 68  | 64  |  | 72  | 67  | 63  |  | 70  |
| 7   | 80  | 70  | 64  | 59  | 79  | 70  | 64  | 59  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 66  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 55  |  | 63  | 58  | 54  |  | 62  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 52  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  |  | 56  | 51  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 376483 |
| 5°  | 359255 |
| 10° | 341811 |
| 15° | 332669 |
| 20° | 320395 |
| 25° | 303211 |
| 30° | 282018 |
| 35° | 236908 |
| 40° | 152686 |
| 45° | 70953  |
| 50° | 18626  |
| 55° | 4626   |
| 60° | 4649   |
| 65° | 3943   |
| 70° | 3911   |
| 75° | 3813   |
| 80° | 3788   |
| 85° | 3774   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 70953 cd/sqm

TEST NUMBER: P1266006

CATALOG NUMBER: P3A20R709730D010 E3CD1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 152.8  | 8.1       |
| 10°-20°   | 411.8  | 21.7      |
| 20°-30°   | 575.3  | 30.3      |
| 30°-40°   | 533.4  | 28.1      |
| 40°-50°   | 191.2  | 10.1      |
| 50°-60°   | 16.2   | 0.9       |
| 60°-70°   | 8.1    | 0.4       |
| 70°-80°   | 5.2    | 0.3       |
| 80°-90°   | 2.0    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1139.8 | 60.1      |
| 0°-40°    | 1673.2 | 88.3      |
| 0°-60°    | 1880.7 | 99.2      |
| 0°-90°    | 1896.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1896.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1717 |      |
| 5°  | 1632 | 153  |
| 15° | 1465 | 412  |
| 25° | 1253 | 575  |
| 35° | 885  | 533  |
| 45° | 229  | 191  |
| 55° | 12   | 16   |
| 65° | 8    | 8    |
| 75° | 4    | 5    |
| 85° | 2    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1266006

CATALOG NUMBER: P3A20R709730D010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1716.9 |
| 2.5°  | 1691.2 |
| 5°    | 1632.1 |
| 7.5°  | 1577.5 |
| 10°   | 1535.1 |
| 12.5° | 1500.2 |
| 15°   | 1465.4 |
| 17.5° | 1423.0 |
| 20°   | 1373.0 |
| 22.5° | 1315.4 |
| 25°   | 1253.2 |
| 27.5° | 1189.6 |
| 30°   | 1113.8 |
| 32.5° | 1016.8 |
| 35°   | 885.0  |
| 37.5° | 716.8  |
| 40°   | 533.4  |
| 42.5° | 363.7  |
| 45°   | 228.8  |
| 47.5° | 127.3  |
| 50°   | 54.6   |
| 52.5° | 18.2   |
| 55°   | 12.1   |
| 57.5° | 10.6   |
| 60°   | 10.6   |
| 62.5° | 9.1    |
| 65°   | 7.6    |
| 67.5° | 7.6    |
| 70°   | 6.1    |
| 72.5° | 6.1    |
| 75°   | 4.5    |
| 77.5° | 4.5    |
| 80°   | 3.0    |
| 82.5° | 3.0    |
| 85°   | 1.5    |
| 87.5° | 1.5    |
| 90°   | 0.0    |

(END OF REPORT)