

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267803

Luminaire Tested: P3A17R309735DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R309735DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 933.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267803

CATALOG NUMBER: P3A17R309735DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267803

CATALOG NUMBER: P3A17R309735DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56
9	68	57	50	45	66	56	49	45	55	49	45		54	49	45		53
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229894
5°	219744
10°	189531
15°	157095
20°	128788
25°	103821
30°	83684
35°	68556
40°	56964
45°	48284
50°	41312
55°	35707
60°	31883
65°	27811
70°	24427
75°	20503
80°	15280
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 48284 cd/sqm

TEST NUMBER: P1267803

CATALOG NUMBER: P3A17R309735DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	9.7
10°-20°	193.0	20.7
20°-30°	197.8	21.2
30°-40°	161.7	17.3
40°-50°	120.9	13.0
50°-60°	84.9	9.1
60°-70°	53.5	5.7
70°-80°	25.7	2.8
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.3	51.6
0°-40°	643.0	68.9
0°-60°	848.9	91.0
0°-90°	933.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	933.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1048	
5°	998	90
15°	692	193
25°	429	198
35°	256	162
45°	156	121
55°	93	85
65°	54	53
75°	24	26
85°	4	5
90°	0	

TEST NUMBER: P1267803

CATALOG NUMBER: P3A17R309735DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1048.4
2.5°	1038.1
5°	998.3
7.5°	932.5
10°	851.2
12.5°	771.6
15°	692.0
17.5°	619.4
20°	551.9
22.5°	487.9
25°	429.1
27.5°	377.2
30°	330.5
32.5°	292.4
35°	256.1
37.5°	226.6
40°	199.0
42.5°	176.5
45°	155.7
47.5°	136.7
50°	121.1
52.5°	107.3
55°	93.4
57.5°	83.0
60°	72.7
62.5°	62.3
65°	53.6
67.5°	45.0
70°	38.1
72.5°	31.1
75°	24.2
77.5°	17.3
80°	12.1
82.5°	6.9
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)