

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263695

Luminaire Tested: P3A02R109730DE010 E3B1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R109730DE010 E3B1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 97CRI , E3B1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.18 / 0.18 / 0.18
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263695

CATALOG NUMBER: P3A02R109730DE010 E3B1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1263695

CATALOG NUMBER: P3A02R109730DE010 E3B1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101	101	100		99
2	113	110	108	106	111	109	107	105	106	104	103		103	102	101		100	99	98		97
3	111	107	104	102	109	106	103	101	104	102	100		101	100	98		99	98	97		96
4	109	105	102	99	107	104	101	99	102	99	98		100	98	97		98	97	96		95
5	107	102	99	97	105	101	99	97	100	98	96		99	97	95		97	96	94		93
6	105	100	97	95	104	100	97	95	98	96	94		97	95	94		96	94	93		92
7	103	99	96	93	102	98	95	93	97	95	93		96	94	92		95	93	92		91
8	102	97	94	92	101	97	94	92	96	93	92		95	93	91		94	92	91		90
9	100	96	93	91	100	95	93	91	95	92	90		94	92	90		93	91	90		89
10	99	94	92	90	98	94	91	90	94	91	89		93	91	89		92	91	89		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1168174
5°	603476
10°	118591
15°	37344
20°	16311
25°	7210
30°	3874
35°	2061
40°	744
45°	279
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 292 cd/sqm

TEST NUMBER: P1263695

CATALOG NUMBER: P3A02R109730DE010 E3B1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.4	71.5
10°-20°	52.4	20.3
20°-30°	15.3	5.9
30°-40°	5.0	1.9
40°-50°	0.9	0.4
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	252.1	97.7
0°-40°	257.1	99.6
0°-60°	258.0	100.0
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5327	
5°	2742	184
15°	164	52
25°	30	15
35°	8	5
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1263695

CATALOG NUMBER: P3A02R109730DE010 E3B1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5327.3
1°	5173.9
2°	4772.5
3°	4142.7
4°	3454.1
5°	2741.6
6°	2067.5
7°	1497.4
8°	1053.4
9°	740.6
10°	532.6
11°	394.6
12°	303.4
13°	243.7
14°	198.6
15°	164.5
17.5°	109.1
20°	69.9
22.5°	44.3
25°	29.8
27.5°	21.3
30°	15.3
32.5°	11.1
35°	7.7
37.5°	5.1
40°	2.6
42.5°	1.7
45°	0.9
47.5°	0.9
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1263695
CATALOG NUMBER: P3A02R109730DE010 E3B1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)