

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263767

Luminaire Tested: P3A02R159730DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1263767  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R159730DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 275.9 lumens  
Efficiency: N/A  
Efficacy: 76.6 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263767  
CATALOG NUMBER: P3A02R159730DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1263767  
 CATALOG NUMBER: P3A02R159730DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96		
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	107	103	100	97	106	102	99	97	100	97	96	98	96	94	97	95	93	92		
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91		
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89		
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88		
8	99	94	91	88	98	93	90	88	93	90	88	92	89	87	91	89	87	86		
9	97	92	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85		
10	96	90	87	85	95	90	87	85	90	87	85	89	86	85	88	86	85	84		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	536470
5°	449614
10°	211797
15°	63860
20°	23615
25°	9194
30°	3418
35°	1044
40°	372
45°	217
50°	136
55°	153
60°	175
65°	104
70°	128
75°	169
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 217 cd/sqm



TEST NUMBER: P1263767  
 CATALOG NUMBER: P3A02R159730DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.9	57.2
10°-20°	93.9	34.0
20°-30°	19.7	7.1
30°-40°	3.2	1.1
40°-50°	0.5	0.2
50°-60°	0.4	0.1
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.5	98.4
0°-40°	274.7	99.5
0°-60°	275.6	99.9
0°-90°	275.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2446	
5°	2043	158
15°	281	94
25°	38	20
35°	4	3
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263767  
CATALOG NUMBER: P3A02R159730DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2446.5
1°	2438.9
2°	2400.1
3°	2322.4
4°	2208.5
5°	2042.6
6°	1847.8
7°	1625.0
8°	1412.2
9°	1171.3
10°	951.2
12.5°	513.2
15°	281.3
17.5°	164.7
20°	101.2
22.5°	62.0
25°	38.0
27.5°	22.9
30°	13.5
32.5°	7.6
35°	3.9
37.5°	2.2
40°	1.3
42.5°	0.9
45°	0.7
47.5°	0.4
50°	0.4
52.5°	0.4
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)