

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267986

Luminaire Tested: P3A17R659735DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R659735DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1203.0 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267986

CATALOG NUMBER: P3A17R659735DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1267986

CATALOG NUMBER: P3A17R659735DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283705
5°	280299
10°	269668
15°	252601
20°	227193
25°	192930
30°	150884
35°	107532
40°	70360
45°	43508
50°	22072
55°	7799
60°	6842
65°	6849
70°	6155
75°	6100
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43508 cd/sqm

TEST NUMBER: P1267986

CATALOG NUMBER: P3A17R659735DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.6	9.9
10°-20°	309.7	25.7
20°-30°	361.9	30.1
30°-40°	252.9	21.0
40°-50°	111.3	9.3
50°-60°	24.8	2.1
60°-70°	12.6	1.0
70°-80°	7.6	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	791.2	65.8
0°-40°	1044.1	86.8
0°-60°	1180.2	98.1
0°-90°	1203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1203.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1294	
5°	1273	120
15°	1113	310
25°	797	362
35°	402	253
45°	140	111
55°	20	25
65°	13	13
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1267986

CATALOG NUMBER: P3A17R659735DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1293.8
2.5°	1289.0
5°	1273.4
7.5°	1247.0
10°	1211.1
12.5°	1166.7
15°	1112.7
17.5°	1046.8
20°	973.6
22.5°	890.9
25°	797.4
27.5°	699.1
30°	595.9
32.5°	496.4
35°	401.7
37.5°	318.9
40°	245.8
42.5°	185.9
45°	140.3
47.5°	103.1
50°	64.7
52.5°	33.6
55°	20.4
57.5°	18.0
60°	15.6
62.5°	14.4
65°	13.2
67.5°	10.8
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)