

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268023

Luminaire Tested: P3A17R709735DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R709735DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 862.0 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268023
CATALOG NUMBER: P3A17R709735DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268023
 CATALOG NUMBER: P3A17R709735DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	9.8
10°-20°	208.2	24.2
20°-30°	237.1	27.5
30°-40°	185.4	21.5
40°-50°	91.1	10.6
50°-60°	28.0	3.3
60°-70°	16.6	1.9
70°-80°	8.9	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.4	61.4
0°-40°	714.8	82.9
0°-60°	833.9	96.7
0°-90°	862.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	862.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	922	
5°	902	84
15°	748	208
25°	518	237
35°	297	185
45°	116	91
55°	29	28
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1268023
CATALOG NUMBER: P3A17R709735DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	922.1
2.5°	917.3
5°	901.7
7.5°	876.5
10°	840.5
12.5°	798.6
15°	748.2
17.5°	694.2
20°	636.7
22.5°	576.7
25°	518.0
27.5°	460.4
30°	405.3
32.5°	350.1
35°	297.4
37.5°	247.0
40°	199.0
42.5°	154.7
45°	116.3
47.5°	81.5
50°	52.8
52.5°	34.8
55°	28.8
57.5°	25.2
60°	21.6
62.5°	19.2
65°	16.8
67.5°	14.4
70°	12.0
72.5°	9.6
75°	8.4
77.5°	7.2
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)