

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426768

Luminaire Tested: P3A17RH9735DE010 E3HY1WMH

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17RH9735DE010 E3HY1WMH
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 97CRI , E3HY1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 733.0 lumens
Efficiency: N/A
Efficacy: 34.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426768

CATALOG NUMBER: P3A17RH9735DE010 E3HY1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1426768

CATALOG NUMBER: P3A17RH9735DE010 E3HY1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	104	100	98	100	98	96		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87
5	96	89	84	81	95	88	84	80	87	83	79		85	82	79		84
6	93	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	69	65	73	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	366374
5°	332136
10°	287637
15°	261409
20°	145823
25°	90537
30°	72593
35°	39485
40°	19923
45°	8931
50°	2866
55°	459
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8931 cd/sqm

TEST NUMBER: P1426768

CATALOG NUMBER: P3A17RH9735DE010 E3HY1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.9	18.7
10°-20°	291.9	39.8
20°-30°	179.5	24.5
30°-40°	98.0	13.4
40°-50°	24.6	3.3
50°-60°	2.2	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.3	83.0
0°-40°	706.2	96.3
0°-60°	733.0	100.0
0°-90°	733.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	733.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1671	
5°	1509	137
15°	1152	292
25°	374	180
35°	148	98
45°	29	25
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426768

CATALOG NUMBER: P3A17RH9735DE010 E3HY1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1670.8
2.5°	1628.8
5°	1508.9
7.5°	1381.7
10°	1291.8
12.5°	1223.4
15°	1151.5
17.5°	916.4
20°	624.9
22.5°	418.6
25°	374.2
27.5°	334.6
30°	286.7
32.5°	214.7
35°	147.5
37.5°	100.8
40°	69.6
42.5°	46.8
45°	28.8
47.5°	15.6
50°	8.4
52.5°	3.6
55°	1.2
57.5°	1.2
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)