

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268099

Luminaire Tested: P3A20R209735D010 E3D1H

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268099  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R209735D010 E3D1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1974.0 lumens  
Efficiency: N/A  
Efficacy: 68.5 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268099

CATALOG NUMBER: P3A20R209735D010 E3D1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1268099

CATALOG NUMBER: P3A20R209735D010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 114 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 |  | 104 | 103 | 102 |  | 100 |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 105 | 103 | 104 | 102 | 101 |  | 101 | 100 | 98  |  | 99  |
| 3   | 109 | 105 | 102 | 99  | 107 | 104 | 101 | 98  | 101 | 99  | 97  |  | 99  | 97  | 95  |  | 97  |
| 4   | 106 | 101 | 98  | 95  | 105 | 100 | 97  | 95  | 99  | 96  | 94  |  | 97  | 95  | 93  |  | 95  |
| 5   | 104 | 98  | 95  | 92  | 102 | 98  | 94  | 92  | 96  | 93  | 91  |  | 95  | 92  | 90  |  | 93  |
| 6   | 101 | 96  | 92  | 89  | 100 | 95  | 92  | 89  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 92  |
| 7   | 99  | 93  | 90  | 87  | 98  | 93  | 89  | 87  | 92  | 89  | 86  |  | 91  | 88  | 86  |  | 90  |
| 8   | 97  | 91  | 87  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 9   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 83  | 88  | 85  | 83  |  | 87  | 84  | 83  |  | 87  |
| 10  | 93  | 87  | 84  | 81  | 92  | 87  | 83  | 81  | 86  | 83  | 81  |  | 86  | 83  | 81  |  | 85  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2994387 |
| 5°  | 2521147 |
| 10° | 1574698 |
| 15° | 588721  |
| 20° | 202084  |
| 25° | 84223   |
| 30° | 39677   |
| 35° | 17775   |
| 40° | 8387    |
| 45° | 4311    |
| 50° | 1569    |
| 55° | 306     |
| 60° | 351     |
| 65° | 415     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4311 cd/sqm

TEST NUMBER: P1268099

CATALOG NUMBER: P3A20R209735D010 E3D1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 952.5  | 48.2      |
| 10°-20°   | 784.6  | 39.7      |
| 20°-30°   | 178.3  | 9.0       |
| 30°-40°   | 45.4   | 2.3       |
| 40°-50°   | 11.4   | 0.6       |
| 50°-60°   | 1.5    | 0.1       |
| 60°-70°   | 0.5    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1915.3 | 97.0      |
| 0°-40°    | 1960.7 | 99.3      |
| 0°-60°    | 1973.6 | 100.0     |
| 0°-90°    | 1974.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1974.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 13656 |      |
| 5°  | 11454 | 952  |
| 15° | 2593  | 785  |
| 25° | 348   | 178  |
| 35° | 66    | 45   |
| 45° | 14    | 11   |
| 55° | 1     | 1    |
| 65° | 1     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1268099

CATALOG NUMBER: P3A20R209735D010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 13655.5 |
| 1°    | 13539.8 |
| 2°    | 13198.6 |
| 3°    | 12709.3 |
| 4°    | 12108.9 |
| 5°    | 11453.6 |
| 6°    | 10723.5 |
| 7°    | 9917.7  |
| 8°    | 8977.6  |
| 9°    | 8046.1  |
| 10°   | 7072.1  |
| 11°   | 6035.5  |
| 12°   | 5000.5  |
| 13°   | 4123.8  |
| 14°   | 3285.6  |
| 15°   | 2593.3  |
| 16°   | 2046.8  |
| 17°   | 1614.6  |
| 18°   | 1297.4  |
| 19°   | 1055.1  |
| 20°   | 866.0   |
| 21°   | 724.0   |
| 22°   | 604.3   |
| 23°   | 502.4   |
| 24°   | 419.1   |
| 25°   | 348.1   |
| 27.5° | 227.7   |
| 30°   | 156.7   |
| 32.5° | 96.5    |
| 35°   | 66.4    |
| 37.5° | 42.4    |
| 40°   | 29.3    |
| 42.5° | 20.1    |
| 45°   | 13.9    |
| 47.5° | 9.3     |
| 50°   | 4.6     |
| 52.5° | 2.3     |
| 55°   | 0.8     |
| 57.5° | 0.8     |
| 60°   | 0.8     |
| 62.5° | 0.8     |
| 65°   | 0.8     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |



TEST NUMBER: P1268099  
CATALOG NUMBER: P3A20R209735D010 E3D1H

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)