

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263888

Luminaire Tested: P3A02R359730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R359730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 113.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263888
CATALOG NUMBER: P3A02R359730DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1263888

CATALOG NUMBER: P3A02R359730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	72	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56991
5°	54765
10°	47717
15°	36550
20°	24455
25°	14807
30°	8482
35°	4738
40°	2519
45°	1302
50°	614
55°	497
60°	482
65°	415
70°	385
75°	339
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1302 cd/sqm



TEST NUMBER: P1263888
 CATALOG NUMBER: P3A02R359730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.6	20.0
10°-20°	43.9	38.8
20°-30°	28.7	25.4
30°-40°	11.6	10.3
40°-50°	3.5	3.1
50°-60°	1.2	1.1
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.2	84.3
0°-40°	106.9	94.6
0°-60°	111.6	98.8
0°-90°	113.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	113.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	249	23
15°	161	44
25°	61	29
35°	18	12
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263888
CATALOG NUMBER: P3A02R359730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	259.9
1°	259.5
2°	258.3
3°	255.9
4°	253.1
5°	248.8
6°	243.5
7°	237.4
8°	230.7
9°	222.9
10°	214.3
11°	204.8
12°	194.8
13°	183.6
14°	172.9
15°	161.0
17.5°	132.1
20°	104.8
22.5°	80.6
25°	61.2
27.5°	45.6
30°	33.5
32.5°	24.6
35°	17.7
37.5°	12.6
40°	8.8
42.5°	6.1
45°	4.2
47.5°	2.8
50°	1.8
52.5°	1.4
55°	1.3
57.5°	1.2
60°	1.1
62.5°	1.0
65°	0.8
67.5°	0.6
70°	0.6
72.5°	0.5
75°	0.4
77.5°	0.3
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1263888
CATALOG NUMBER: P3A02R359730DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)