

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263897

Luminaire Tested: P3A02R359730DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263897  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R359730DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 177.0 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263897  
CATALOG NUMBER: P3A02R359730DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1263897

CATALOG NUMBER: P3A02R359730DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	40435
5°	39577
10°	37051
15°	33258
20°	28936
25°	24655
30°	20661
35°	16463
40°	11908
45°	7536
50°	4094
55°	2829
60°	2675
65°	2491
70°	2372
75°	2033
80°	1894
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7536 cd/sqm



TEST NUMBER: P1263897  
 CATALOG NUMBER: P3A02R359730DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.7	9.5
10°-20°	40.8	23.0
20°-30°	46.7	26.4
30°-40°	38.1	21.5
40°-50°	19.2	10.9
50°-60°	7.1	4.0
60°-70°	4.8	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.2	58.9
0°-40°	142.4	80.4
0°-60°	168.7	95.3
0°-90°	177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	177.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	184	
5°	180	17
15°	146	41
25°	102	47
35°	62	38
45°	24	19
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1263897

CATALOG NUMBER: P3A02R359730DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	184.4
1°	184.2
2°	183.7
3°	182.9
4°	181.5
5°	179.8
6°	177.6
7°	175.4
8°	172.6
9°	169.7
10°	166.4
11°	163.0
12°	159.2
13°	155.1
14°	150.7
15°	146.5
17.5°	135.4
20°	124.0
22.5°	112.4
25°	101.9
27.5°	91.6
30°	81.6
32.5°	71.5
35°	61.5
37.5°	51.4
40°	41.6
42.5°	32.4
45°	24.3
47.5°	17.5
50°	12.0
52.5°	8.7
55°	7.4
57.5°	6.8
60°	6.1
62.5°	5.5
65°	4.8
67.5°	4.2
70°	3.7
72.5°	3.1
75°	2.4
77.5°	2.0
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4



TEST NUMBER: P1263897  
CATALOG NUMBER: P3A02R359730DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)