

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263958

Luminaire Tested: P3A02R459730DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R459730DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 158.0 lumens
Efficiency: N/A
Efficacy: 43.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263958

CATALOG NUMBER: P3A02R459730DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1263958

CATALOG NUMBER: P3A02R459730DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86	83	81	79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81	78	75	74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	66	64
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69	65	61	60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58	56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47058
5°	45983
10°	42417
15°	36890
20°	30313
25°	23590
30°	17420
35°	12260
40°	7643
45°	4155
50°	2252
55°	1912
60°	1710
65°	1453
70°	1282
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4155 cd/sqm

TEST NUMBER: P1263958

CATALOG NUMBER: P3A02R459730DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.3	12.2
10°-20°	44.9	28.4
20°-30°	44.6	28.2
30°-40°	28.7	18.2
40°-50°	11.1	7.0
50°-60°	4.5	2.8
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.9	68.9
0°-40°	137.6	87.1
0°-60°	153.2	96.9
0°-90°	158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	158.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	215	
5°	209	19
15°	162	45
25°	98	45
35°	46	29
45°	13	11
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1263958

CATALOG NUMBER: P3A02R459730DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	214.6
2.5°	213.5
5°	208.9
7.5°	201.0
10°	190.5
12.5°	177.4
15°	162.5
17.5°	146.3
20°	129.9
22.5°	113.2
25°	97.5
27.5°	82.6
30°	68.8
32.5°	56.7
35°	45.8
37.5°	35.9
40°	26.7
42.5°	19.3
45°	13.4
47.5°	9.0
50°	6.6
52.5°	5.5
55°	5.0
57.5°	4.4
60°	3.9
62.5°	3.3
65°	2.8
67.5°	2.4
70°	2.0
72.5°	1.8
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)