

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426922

Luminaire Tested: P3A20RH9735D010 E3HY1LI

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20RH9735D010 E3HY1LI
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 97CRI , E3HY1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1203.0 lumens
Efficiency: N/A
Efficacy: 41.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426922

CATALOG NUMBER: P3A20RH9735D010 E3HY1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1426922

CATALOG NUMBER: P3A20RH9735D010 E3HY1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88		92	89	87		90	88	86	85
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88	86	84	82
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86	83	81	80
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84	81	79	78
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		81	79	76	76
10	88	82	78	75	87	81	77	75	81	77	75		80	77	75		79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	846445
5°	819104
10°	747615
15°	638914
20°	250692
25°	57318
30°	25852
35°	3293
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1426922

CATALOG NUMBER: P3A20RH9735D010 E3HY1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.2	28.4
10°-20°	693.3	57.6
20°-30°	151.0	12.5
30°-40°	16.5	1.4
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.5	98.6
0°-40°	1203.0	100.0
0°-60°	1203.0	100.0
0°-90°	1203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1203.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3860	
5°	3721	342
15°	2814	693
25°	237	151
35°	12	16
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426922

CATALOG NUMBER: P3A20RH9735D010 E3HY1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3860.1
2.5°	3880.5
5°	3721.2
7.5°	3504.7
10°	3357.6
12.5°	3173.8
15°	2814.4
17.5°	2042.4
20°	1074.3
22.5°	412.6
25°	236.9
27.5°	159.3
30°	102.1
32.5°	44.9
35°	12.3
37.5°	4.1
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)