

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266151

Luminaire Tested: P3A02R159735DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R159735DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 236.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266151
CATALOG NUMBER: P3A02R159735DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1266151
 CATALOG NUMBER: P3A02R159735DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201607
5°	178956
10°	124268
15°	73485
20°	41864
25°	23929
30°	13243
35°	7067
40°	3893
45°	2109
50°	1330
55°	1032
60°	877
65°	830
70°	705
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2109 cd/sqm



TEST NUMBER: P1266151

CATALOG NUMBER: P3A02R159735DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	29.3
10°-20°	91.2	38.7
20°-30°	47.0	19.9
30°-40°	17.7	7.5
40°-50°	5.8	2.4
50°-60°	2.5	1.1
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.4	87.9
0°-40°	225.0	95.3
0°-60°	233.3	98.8
0°-90°	236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	236.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	919	
5°	813	69
15°	324	91
25°	99	47
35°	26	18
45°	7	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266151
CATALOG NUMBER: P3A02R159735DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	919.4
1°	917.6
2°	905.5
3°	882.6
4°	852.3
5°	813.0
6°	768.4
7°	719.6
8°	665.2
9°	611.6
10°	558.1
12.5°	429.5
15°	323.7
17.5°	242.4
20°	179.4
22.5°	133.9
25°	98.9
27.5°	72.1
30°	52.3
32.5°	37.1
35°	26.4
37.5°	18.9
40°	13.6
42.5°	9.8
45°	6.8
47.5°	5.0
50°	3.9
52.5°	3.2
55°	2.7
57.5°	2.3
60°	2.0
62.5°	1.8
65°	1.6
67.5°	1.4
70°	1.1
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)