

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264046

Luminaire Tested: P3A02R609730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R609730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 159.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264046
CATALOG NUMBER: P3A02R609730DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264046
 CATALOG NUMBER: P3A02R609730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	67	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58			
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40304
5°	39401
10°	36873
15°	33076
20°	28446
25°	23517
30°	18585
35°	13813
40°	9504
45°	5954
50°	3275
55°	1912
60°	1710
65°	1453
70°	1282
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5954 cd/sqm



TEST NUMBER: P1264046
 CATALOG NUMBER: P3A02R609730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.7	10.5
10°-20°	40.5	25.5
20°-30°	44.4	27.9
30°-40°	32.4	20.4
40°-50°	15.3	9.6
50°-60°	5.0	3.1
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	101.5	63.9
0°-40°	133.9	84.2
0°-60°	154.2	97.0
0°-90°	159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	184	
5°	179	17
15°	146	40
25°	97	44
35°	52	32
45°	19	15
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1264046
CATALOG NUMBER: P3A02R609730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	183.8
2.5°	182.7
5°	179.0
7.5°	173.3
10°	165.6
12.5°	156.4
15°	145.7
17.5°	134.2
20°	121.9
22.5°	109.5
25°	97.2
27.5°	85.0
30°	73.4
32.5°	62.3
35°	51.6
37.5°	42.0
40°	33.2
42.5°	25.6
45°	19.2
47.5°	14.0
50°	9.6
52.5°	6.3
55°	5.0
57.5°	4.4
60°	3.9
62.5°	3.3
65°	2.8
67.5°	2.4
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)