

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266193

Luminaire Tested: P3A02R209735DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R209735DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 205.0 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266193

CATALOG NUMBER: P3A02R209735DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266193

CATALOG NUMBER: P3A02R209735DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	104	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	104	102	102	101	100	100	99	98	97		
3	110	107	104	101	109	105	103	101	103	101	99	101	99	98	99	97	96	95		
4	108	104	101	98	107	103	100	98	101	98	97	99	97	95	97	96	94	93		
5	106	101	98	96	105	100	97	95	99	96	94	97	95	94	96	94	93	92		
6	104	99	96	93	103	98	95	93	97	94	93	96	94	92	95	93	91	91		
7	102	97	94	92	101	96	93	91	95	93	91	95	92	90	94	92	90	89		
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88		
9	99	94	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87		
10	97	92	89	87	96	92	89	87	91	88	87	91	88	87	90	88	86	86		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407643
5°	313096
10°	192893
15°	56141
20°	7491
25°	2226
30°	658
35°	80
40°	86
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1266193

CATALOG NUMBER: P3A02R209735DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.5	57.8
10°-20°	80.8	39.4
20°-30°	5.2	2.5
30°-40°	0.5	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.5	99.7
0°-40°	205.0	100.0
0°-60°	205.0	100.0
0°-90°	205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	205.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1859	
5°	1422	118
15°	247	81
25°	9	5
35°	0	0
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266193

CATALOG NUMBER: P3A02R209735DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1859.0
2.5°	1676.3
5°	1422.4
7.5°	1141.1
10°	866.3
12.5°	543.4
15°	247.3
17.5°	78.3
20°	32.1
22.5°	17.0
25°	9.2
27.5°	4.6
30°	2.6
32.5°	1.3
35°	0.3
37.5°	0.3
40°	0.3
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)