

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266298

Luminaire Tested: P3A02R409735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R409735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 318.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266298

CATALOG NUMBER: P3A02R409735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266298

CATALOG NUMBER: P3A02R409735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162092
5°	160928
10°	156711
15°	139978
20°	92828
25°	34768
30°	9293
35°	3641
40°	1317
45°	620
50°	205
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 620 cd/sqm

TEST NUMBER: P1266298

CATALOG NUMBER: P3A02R409735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	21.7
10°-20°	163.4	51.4
20°-30°	74.1	23.3
30°-40°	9.6	3.0
40°-50°	1.7	0.5
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.5	96.4
0°-40°	316.1	99.4
0°-60°	317.9	100.0
0°-90°	318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	318.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	739	
5°	731	69
15°	617	163
25°	144	74
35°	14	10
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266298

CATALOG NUMBER: P3A02R409735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	739.2
1°	738.8
2°	737.6
3°	736.0
4°	733.9
5°	731.1
6°	727.8
7°	723.8
8°	718.9
9°	712.3
10°	703.8
11°	693.9
12°	680.6
13°	664.3
14°	642.9
15°	616.6
16°	583.1
17°	544.9
18°	499.1
19°	450.6
20°	397.8
21°	344.9
22°	292.8
23°	240.9
24°	189.9
25°	143.7
26°	106.4
27°	77.9
28°	58.6
29°	45.5
30°	36.7
31°	30.4
32°	25.4
32.5°	23.2
33°	20.9
34°	17.0
35°	13.6
36°	10.7
37°	8.5
37.5°	7.6
38°	6.7
39°	5.6
40°	4.6
42.5°	3.0
45°	2.0



TEST NUMBER: P1266298

CATALOG NUMBER: P3A02R409735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.2
50°	0.6
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)