

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266375

Luminaire Tested: P3A02R559735DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R559735DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 302.1 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266375

CATALOG NUMBER: P3A02R559735DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1266375

CATALOG NUMBER: P3A02R559735DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94	92	90	89
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90	87	85	84
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		85	83	80	79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76	74
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78	74	72	70
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83765
5°	82985
10°	86327
15°	85108
20°	78500
25°	63875
30°	38791
35°	13438
40°	3836
45°	1830
50°	785
55°	344
60°	395
65°	363
70°	321
75°	424
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1830 cd/sqm

TEST NUMBER: P1266375

CATALOG NUMBER: P3A02R559735DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.4	12.1
10°-20°	104.2	34.5
20°-30°	116.2	38.5
30°-40°	38.0	12.6
40°-50°	5.0	1.7
50°-60°	1.1	0.4
60°-70°	0.6	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.8	85.0
0°-40°	294.9	97.6
0°-60°	300.9	99.6
0°-90°	302.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	302.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	382	
5°	377	36
15°	375	104
25°	264	116
35°	50	38
45°	6	5
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266375

CATALOG NUMBER: P3A02R559735DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	382.0
2.5°	379.3
5°	377.0
7.5°	382.4
10°	387.7
12.5°	384.9
15°	374.9
17.5°	359.1
20°	336.4
22.5°	305.0
25°	264.0
27.5°	211.8
30°	153.2
32.5°	94.0
35°	50.2
37.5°	25.4
40°	13.4
42.5°	8.6
45°	5.9
47.5°	4.1
50°	2.3
52.5°	1.4
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.7
65°	0.7
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)