

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264317

Luminaire Tested: P3A05R359730DE010 E3PH1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264317  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R359730DE010 E3PH1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3PH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 521.0 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264317  
CATALOG NUMBER: P3A05R359730DE010 E3PH1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264317  
 CATALOG NUMBER: P3A05R359730DE010 E3PH1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	91	90	89
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87	86	85
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	81	80
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80	79	78
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77	76	75
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75	74	73
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	376395	376395	376395
5°	369931	369138	368346
10°	339027	328852	320858
15°	242771	235030	232169
20°	112570	116443	120527
25°	26711	38010	39631
30°	7849	8989	10103
35°	1794	2891	2650
40°	372	773	515
45°	124	124	124
50°	136	0	136
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 144 cd/sqm



TEST NUMBER: P1264317  
 CATALOG NUMBER: P3A05R359730DE010 E3PH1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.1	29.6
10°-20°	275.5	52.9
20°-30°	82.9	15.9
30°-40°	7.9	1.5
40°-50°	0.5	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.5	98.4
0°-40°	520.4	99.9
0°-60°	521.0	100.0
0°-90°	521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	521.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1681	1680	1677	1675	1673	156
15°	1069	1061	1035	1031	1023	282
25°	110	122	157	164	164	71
35°	7	9	11	12	10	6
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1264317  
 CATALOG NUMBER: P3A05R359730DE010 E3PH1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1716.5	1716.5	1716.5	1716.5	1716.5
1°	1715.6	1715.6	1714.7	1714.7	1712.9
2°	1711.6	1712.0	1710.2	1709.8	1708.4
3°	1705.3	1703.9	1703.9	1703.1	1702.2
4°	1695.4	1692.7	1691.8	1692.3	1690.5
5°	1680.6	1680.2	1677.0	1674.8	1673.4
6°	1664.5	1661.3	1654.6	1648.8	1647.4
7°	1640.2	1633.5	1627.7	1615.5	1613.7
8°	1610.6	1599.8	1587.3	1570.2	1569.3
9°	1574.3	1556.8	1539.3	1516.4	1508.3
10°	1522.6	1506.5	1476.9	1456.7	1441.0
11°	1458.5	1438.3	1403.7	1379.5	1366.5
12°	1385.8	1366.9	1326.5	1304.6	1286.2
13°	1292.4	1276.7	1239.0	1214.8	1200.4
14°	1184.3	1172.6	1136.7	1125.9	1121.0
15°	1069.4	1061.3	1035.3	1030.8	1022.7
17.5°	787.1	773.7	758.9	761.5	764.2
20°	482.4	501.3	499.0	508.9	516.5
22.5°	240.5	264.8	293.0	310.1	318.6
25°	110.4	121.6	157.1	163.8	163.8
27.5°	55.6	58.3	74.0	75.4	79.0
30°	31.0	33.2	35.5	39.5	39.9
32.5°	15.7	18.4	19.3	21.5	20.6
35°	6.7	9.0	10.8	11.7	9.9
37.5°	3.1	4.0	5.8	5.4	4.0
40°	1.3	1.8	2.7	2.2	1.8
42.5°	0.9	0.9	1.3	0.9	0.9
45°	0.4	0.4	0.4	0.4	0.4
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.0	0.0	0.0	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1264317  
CATALOG NUMBER: P3A05R359730DE010 E3PH1MW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)