

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266402

Luminaire Tested: P3A02R609735DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R609735DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 293.0 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266402

CATALOG NUMBER: P3A02R609735DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266402

CATALOG NUMBER: P3A02R609735DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	78	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		78	70	64	60		69	64	60		68	63	60		67	62	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69972
5°	67202
10°	69182
15°	70057
20°	61862
25°	52140
30°	42285
35°	27546
40°	12652
45°	4838
50°	1637
55°	421
60°	395
65°	363
70°	321
75°	424
80°	253
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4838 cd/sqm

TEST NUMBER: P1266402

CATALOG NUMBER: P3A02R609735DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.4	10.0
10°-20°	84.5	28.8
20°-30°	98.6	33.6
30°-40°	63.6	21.7
40°-50°	14.3	4.9
50°-60°	1.4	0.5
60°-70°	0.7	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.5	72.5
0°-40°	276.1	94.2
0°-60°	291.8	99.6
0°-90°	293.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	293.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	319	
5°	305	29
15°	309	85
25°	216	99
35°	103	64
45°	16	14
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266402

CATALOG NUMBER: P3A02R609735DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	319.1
2.5°	313.9
5°	305.3
7.5°	304.8
10°	310.7
12.5°	314.5
15°	308.6
17.5°	291.0
20°	265.1
22.5°	238.2
25°	215.5
27.5°	193.3
30°	167.0
32.5°	136.2
35°	102.9
37.5°	70.3
40°	44.2
42.5°	26.5
45°	15.6
47.5°	9.1
50°	4.8
52.5°	1.6
55°	1.1
57.5°	0.9
60°	0.9
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)