

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266546

Luminaire Tested: P3A05R129735DE010 E3PH1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R129735DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 454.0 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266546

CATALOG NUMBER: P3A05R129735DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266546

CATALOG NUMBER: P3A05R129735DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	98	97
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98	95	94
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	95	92	91
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	94	91	90
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	92	90	89
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	90	88	88
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	89	87	87
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	88	86	86
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	87	85	85
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	85	83	83
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1466659
5°	947653
10°	267374
15°	75596
20°	31619
25°	14009
30°	7140
35°	3774
40°	1603
45°	434
50°	478
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 478 cd/sqm

TEST NUMBER: P1266546

CATALOG NUMBER: P3A05R129735DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.3	66.8
10°-20°	110.1	24.2
20°-30°	29.5	6.5
30°-40°	9.3	2.0
40°-50°	1.7	0.4
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	442.9	97.5
0°-40°	452.1	99.6
0°-60°	454.0	100.0
0°-90°	454.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	454.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6688	
5°	4305	303
15°	333	110
25°	58	29
35°	14	9
45°	1	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266546

CATALOG NUMBER: P3A05R129735DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6688.5
1°	6575.6
2°	6258.1
3°	5714.9
4°	5040.4
5°	4305.2
6°	3539.0
7°	2853.2
8°	2195.6
9°	1634.0
10°	1200.8
11°	884.7
12°	666.0
13°	516.5
14°	409.2
15°	333.0
17.5°	211.7
20°	135.5
22.5°	87.5
25°	57.9
27.5°	39.5
30°	28.2
32.5°	19.8
35°	14.1
37.5°	9.9
40°	5.6
42.5°	2.8
45°	1.4
47.5°	1.4
50°	1.4
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1266546

CATALOG NUMBER: P3A05R129735DE010 E3PH1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)