

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264361

Luminaire Tested: P3A05R459730DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R459730DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 501.9 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264361
CATALOG NUMBER: P3A05R459730DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1264361
 CATALOG NUMBER: P3A05R459730DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188516
5°	184107
10°	169224
15°	143406
20°	111263
25°	77763
30°	48995
35°	28830
40°	16316
45°	7939
50°	2763
55°	2217
60°	2149
65°	2075
70°	1988
75°	1864
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7939 cd/sqm



TEST NUMBER: P1264361
 CATALOG NUMBER: P3A05R459730DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	15.4
10°-20°	173.5	34.6
20°-30°	147.3	29.3
30°-40°	70.3	14.0
40°-50°	21.2	4.2
50°-60°	5.4	1.1
60°-70°	4.0	0.8
70°-80°	2.3	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.2	79.3
0°-40°	468.4	93.3
0°-60°	495.0	98.6
0°-90°	501.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	860	
5°	836	77
15°	632	173
25°	321	147
35°	108	70
45°	26	21
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1264361
CATALOG NUMBER: P3A05R459730DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	859.7
2.5°	854.3
5°	836.4
7.5°	805.4
10°	760.0
12.5°	699.9
15°	631.7
17.5°	555.8
20°	476.8
22.5°	396.4
25°	321.4
27.5°	253.2
30°	193.5
32.5°	145.5
35°	107.7
37.5°	79.5
40°	57.0
42.5°	39.5
45°	25.6
47.5°	14.4
50°	8.1
52.5°	6.3
55°	5.8
57.5°	5.4
60°	4.9
62.5°	4.5
65°	4.0
67.5°	3.6
70°	3.1
72.5°	2.7
75°	2.2
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)