

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264391

Luminaire Tested: P3A05R509730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R509730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 193.0 lumens
Efficiency: N/A
Efficacy: 26.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264391

CATALOG NUMBER: P3A05R509730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264391

CATALOG NUMBER: P3A05R509730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39229
5°	38653
10°	36940
15°	34211
20°	30733
25°	27026
30°	22991
35°	18631
40°	13998
45°	9024
50°	4298
55°	3364
60°	3201
65°	2958
70°	2693
75°	2457
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9024 cd/sqm

TEST NUMBER: P1264391

CATALOG NUMBER: P3A05R509730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.5	8.5
10°-20°	42.0	21.8
20°-30°	51.0	26.4
30°-40°	43.3	22.4
40°-50°	22.5	11.7
50°-60°	8.1	4.2
60°-70°	5.6	2.9
70°-80°	3.1	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.5	56.7
0°-40°	152.8	79.2
0°-60°	183.4	95.0
0°-90°	193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	193.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	179	
5°	176	16
15°	151	42
25°	112	51
35°	70	43
45°	29	22
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264391

CATALOG NUMBER: P3A05R509730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	178.9
2.5°	178.2
5°	175.6
7.5°	171.6
10°	165.9
12.5°	158.6
15°	150.7
17.5°	141.6
20°	131.7
22.5°	121.6
25°	111.7
27.5°	101.3
30°	90.8
32.5°	80.2
35°	69.6
37.5°	59.3
40°	48.9
42.5°	39.0
45°	29.1
47.5°	19.4
50°	12.6
52.5°	9.7
55°	8.8
57.5°	7.9
60°	7.3
62.5°	6.4
65°	5.7
67.5°	4.8
70°	4.2
72.5°	3.5
75°	2.9
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)