

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264416

Luminaire Tested: P3A05R559730DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R559730DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 488.9 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264416
CATALOG NUMBER: P3A05R559730DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264416

CATALOG NUMBER: P3A05R559730DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	95	90	86	92	88	85	89	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134266
5°	132907
10°	128365
15°	118639
20°	102372
25°	80860
30°	57351
35°	36995
40°	22213
45°	12528
50°	6720
55°	2409
60°	2149
65°	2075
70°	1988
75°	1864
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12528 cd/sqm



TEST NUMBER: P1264416

CATALOG NUMBER: P3A05R559730DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	11.6
10°-20°	144.5	29.6
20°-30°	151.4	31.0
30°-40°	88.4	18.1
40°-50°	33.1	6.8
50°-60°	7.8	1.6
60°-70°	4.0	0.8
70°-80°	2.3	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.7	72.1
0°-40°	441.1	90.2
0°-60°	482.0	98.6
0°-90°	488.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	612	
5°	604	57
15°	523	145
25°	334	151
35°	138	88
45°	40	33
55°	6	8
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1264416

CATALOG NUMBER: P3A05R559730DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	612.3
2.5°	610.6
5°	603.8
7.5°	593.1
10°	576.5
12.5°	553.1
15°	522.6
17.5°	484.0
20°	438.7
22.5°	388.0
25°	334.2
27.5°	279.0
30°	226.5
32.5°	179.0
35°	138.2
37.5°	105.0
40°	77.6
42.5°	55.6
45°	40.4
47.5°	29.2
50°	19.7
52.5°	11.2
55°	6.3
57.5°	5.4
60°	4.9
62.5°	4.5
65°	4.0
67.5°	3.6
70°	3.1
72.5°	2.7
75°	2.2
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)