

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264467

Luminaire Tested: P3A05R659730DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R659730DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 536.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264467

CATALOG NUMBER: P3A05R659730DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1264467

CATALOG NUMBER: P3A05R659730DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	88		93	89	86		90	87	85		88	86	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	81	78
5	93	85	79	75		92	84	79	75		82	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	70	65		83	75	69	65		73	69	65		72	68	65		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		68	63	60
9	77	67	61	58		76	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143629
5°	133370
10°	128967
15°	124291
20°	114903
25°	104692
30°	80873
35°	46873
40°	18606
45°	7939
50°	1876
55°	268
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7939 cd/sqm

TEST NUMBER: P1264467

CATALOG NUMBER: P3A05R659730DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	10.7
10°-20°	152.5	28.5
20°-30°	193.1	36.0
30°-40°	109.9	20.5
40°-50°	21.9	4.1
50°-60°	1.1	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.8	75.1
0°-40°	512.7	95.7
0°-60°	535.7	99.9
0°-90°	536.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	536.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	655	
5°	606	57
15°	548	153
25°	433	193
35°	175	110
45°	26	22
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1264467

CATALOG NUMBER: P3A05R659730DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	655.0
1°	650.1
2°	639.6
3°	627.2
4°	615.1
5°	605.9
6°	599.0
7°	593.5
8°	588.7
9°	583.8
10°	579.2
11°	574.1
12°	568.8
13°	562.5
14°	555.6
15°	547.5
16°	537.8
17°	527.2
18°	515.7
19°	503.6
20°	492.4
21°	480.9
22°	470.6
23°	459.8
24°	447.2
25°	432.7
26°	415.3
27°	394.4
28°	370.8
29°	345.7
30°	319.4
31°	290.6
32°	261.9
32.5°	247.2
33°	232.9
34°	203.8
35°	175.1
36°	148.7
37°	122.5
37.5°	109.1
38°	98.3
39°	79.5
40°	65.0
42.5°	40.1
45°	25.6



TEST NUMBER: P1264467

CATALOG NUMBER: P3A05R659730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	15.0
50°	5.5
52.5°	1.1
55°	0.7
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)