

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264483

Luminaire Tested: P3A05R659730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R659730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 353.9 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264483

CATALOG NUMBER: P3A05R659730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264483

CATALOG NUMBER: P3A05R659730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	71		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62999
5°	62139
10°	60075
15°	56641
20°	52248
25°	47422
30°	42006
35°	35737
40°	28453
45°	20064
50°	11667
55°	6346
60°	5921
65°	5344
70°	4873
75°	4575
80°	3915
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20064 cd/sqm

TEST NUMBER: P1264483

CATALOG NUMBER: P3A05R659730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.6	7.5
10°-20°	69.8	19.7
20°-30°	89.7	25.3
30°-40°	83.0	23.4
40°-50°	50.1	14.2
50°-60°	17.1	4.8
60°-70°	10.3	2.9
70°-80°	5.8	1.6
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.1	52.6
0°-40°	269.1	76.0
0°-60°	336.2	95.0
0°-90°	353.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	353.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	282	27
15°	250	70
25°	196	90
35°	134	83
45°	65	50
55°	17	17
65°	10	10
75°	5	6
85°	1	2
90°	0	

TEST NUMBER: P1264483

CATALOG NUMBER: P3A05R659730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	287.3
2.5°	285.9
5°	282.3
7.5°	276.9
10°	269.8
12.5°	260.8
15°	249.5
17.5°	237.4
20°	223.9
22.5°	210.0
25°	196.0
27.5°	181.2
30°	165.9
32.5°	150.6
35°	133.5
37.5°	116.9
40°	99.4
42.5°	81.8
45°	64.7
47.5°	49.0
50°	34.2
52.5°	21.6
55°	16.6
57.5°	14.8
60°	13.5
62.5°	11.7
65°	10.3
67.5°	9.0
70°	7.6
72.5°	6.7
75°	5.4
77.5°	4.5
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0

(END OF REPORT)