

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264576

Luminaire Tested: P3A09R159730DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1264576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R159730DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 404.0 lumens  
Efficiency: N/A  
Efficacy: 36.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264576  
CATALOG NUMBER: P3A09R159730DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1264576  
 CATALOG NUMBER: P3A09R159730DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	174218
5°	161017
10°	128544
15°	97095
20°	73950
25°	56350
30°	40361
35°	26341
40°	16145
45°	9768
50°	6482
55°	5008
60°	4298
65°	3736
70°	3334
75°	3304
80°	2526
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9768 cd/sqm



TEST NUMBER: P1264576  
 CATALOG NUMBER: P3A09R159730DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.8	16.0
10°-20°	119.6	29.6
20°-30°	106.4	26.3
30°-40°	63.0	15.6
40°-50°	25.8	6.4
50°-60°	12.1	3.0
60°-70°	7.4	1.8
70°-80°	3.9	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.8	72.0
0°-40°	353.8	87.6
0°-60°	391.7	97.0
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	794	
5°	732	65
15°	428	120
25°	233	106
35°	98	63
45°	32	26
55°	13	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1264576  
CATALOG NUMBER: P3A09R159730DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	794.5
1°	792.5
2°	786.6
3°	774.8
4°	755.1
5°	731.5
6°	705.9
7°	675.7
8°	644.2
9°	612.1
10°	577.3
12.5°	497.9
15°	427.7
17.5°	367.4
20°	316.9
22.5°	272.3
25°	232.9
27.5°	194.8
30°	159.4
32.5°	127.3
35°	98.4
37.5°	75.4
40°	56.4
42.5°	42.0
45°	31.5
47.5°	24.3
50°	19.0
52.5°	15.7
55°	13.1
57.5°	11.2
60°	9.8
62.5°	8.5
65°	7.2
67.5°	6.6
70°	5.2
72.5°	4.6
75°	3.9
77.5°	2.6
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)