

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266687

Luminaire Tested: P3A05R359735DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266687  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R359735DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 376.9 lumens  
Efficiency: N/A  
Efficacy: 52.3 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266687  
CATALOG NUMBER: P3A05R359735DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1266687

CATALOG NUMBER: P3A05R359735DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86112
5°	84283
10°	78934
15°	70852
20°	61629
25°	52527
30°	44007
35°	35041
40°	25333
45°	16033
50°	8733
55°	6040
60°	5701
65°	5292
70°	5065
75°	4321
80°	4167
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16033 cd/sqm



TEST NUMBER: P1266687  
 CATALOG NUMBER: P3A05R359735DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.6	9.5
10°-20°	86.9	23.0
20°-30°	99.5	26.4
30°-40°	81.2	21.5
40°-50°	40.9	10.9
50°-60°	15.2	4.0
60°-70°	10.2	2.7
70°-80°	5.6	1.5
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.0	58.9
0°-40°	303.3	80.5
0°-60°	359.4	95.4
0°-90°	376.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	376.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	393	
5°	383	36
15°	312	87
25°	217	100
35°	131	81
45°	52	41
55°	16	15
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1266687  
CATALOG NUMBER: P3A05R359735DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	392.7
1°	392.3
2°	391.3
3°	389.5
4°	386.7
5°	382.9
6°	378.3
7°	373.6
8°	367.6
9°	361.5
10°	354.5
11°	347.1
12°	339.2
13°	330.3
14°	321.0
15°	312.1
17.5°	288.4
20°	264.1
22.5°	239.5
25°	217.1
27.5°	195.2
30°	173.8
32.5°	152.3
35°	130.9
37.5°	109.5
40°	88.5
42.5°	68.9
45°	51.7
47.5°	37.3
50°	25.6
52.5°	18.6
55°	15.8
57.5°	14.4
60°	13.0
62.5°	11.6
65°	10.2
67.5°	8.9
70°	7.9
72.5°	6.5
75°	5.1
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9



TEST NUMBER: P1266687  
CATALOG NUMBER: P3A05R359735DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)