

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264591

Luminaire Tested: P3A09R209730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R209730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 333.0 lumens
Efficiency: N/A
Efficacy: 30.0 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264591
CATALOG NUMBER: P3A09R209730DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264591
 CATALOG NUMBER: P3A09R209730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	256208
5°	232885
10°	172119
15°	106471
20°	60812
25°	34720
30°	19471
35°	10601
40°	5811
45°	3194
50°	1876
55°	1338
60°	1272
65°	1193
70°	1026
75°	1101
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3194 cd/sqm



TEST NUMBER: P1264591
 CATALOG NUMBER: P3A09R209730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	27.5
10°-20°	130.8	39.3
20°-30°	68.3	20.5
30°-40°	26.4	7.9
40°-50°	8.6	2.6
50°-60°	3.4	1.0
60°-70°	2.2	0.7
70°-80°	1.3	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.7	87.3
0°-40°	317.1	95.2
0°-60°	329.0	98.8
0°-90°	333.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1168	
5°	1058	92
15°	469	131
25°	144	68
35°	40	26
45°	10	9
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1264591
CATALOG NUMBER: P3A09R209730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1168.4
1°	1166.1
2°	1152.3
3°	1131.1
4°	1098.3
5°	1058.0
6°	1010.4
7°	957.7
8°	896.6
9°	837.0
10°	773.0
12.5°	614.4
15°	469.0
17.5°	351.0
20°	260.6
22.5°	193.0
25°	143.5
27.5°	105.8
30°	76.9
32.5°	55.7
35°	39.6
37.5°	28.6
40°	20.3
42.5°	14.5
45°	10.3
47.5°	7.4
50°	5.5
52.5°	4.2
55°	3.5
57.5°	3.2
60°	2.9
62.5°	2.6
65°	2.3
67.5°	1.9
70°	1.6
72.5°	1.6
75°	1.3
77.5°	1.0
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)