

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264722

Luminaire Tested: P3A09R409730DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R409730DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 482.0 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264722
CATALOG NUMBER: P3A09R409730DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1264722
 CATALOG NUMBER: P3A09R409730DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80	80	80	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150076
5°	147039
10°	136916
15°	119320
20°	96165
25°	72077
30°	50666
35°	33194
40°	20095
45°	12001
50°	7164
55°	5773
60°	5175
65°	4410
70°	4231
75°	3304
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12001 cd/sqm



TEST NUMBER: P1264722
 CATALOG NUMBER: P3A09R409730DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	12.9
10°-20°	144.8	30.0
20°-30°	136.4	28.3
30°-40°	78.9	16.4
40°-50°	31.4	6.5
50°-60°	13.9	2.9
60°-70°	8.6	1.8
70°-80°	4.5	0.9
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.2	71.2
0°-40°	422.1	87.6
0°-60°	467.5	97.0
0°-90°	482.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	482.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	684	
5°	668	62
15°	526	145
25°	298	136
35°	124	79
45°	39	31
55°	15	14
65°	8	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1264722
CATALOG NUMBER: P3A09R409730DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	684.4
2.5°	680.5
5°	668.0
7.5°	645.1
10°	614.9
12.5°	574.2
15°	525.6
17.5°	471.2
20°	412.1
22.5°	353.0
25°	297.9
27.5°	246.7
30°	200.1
32.5°	159.5
35°	124.0
37.5°	93.8
40°	70.2
42.5°	52.5
45°	38.7
47.5°	28.2
50°	21.0
52.5°	17.1
55°	15.1
57.5°	13.8
60°	11.8
62.5°	9.8
65°	8.5
67.5°	7.2
70°	6.6
72.5°	5.2
75°	3.9
77.5°	3.3
80°	2.6
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)