

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266759

Luminaire Tested: P3A05R509735DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R509735DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 648.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266759

CATALOG NUMBER: P3A05R509735DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1266759

CATALOG NUMBER: P3A05R509735DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	110	108	106		105	104	102		102	101	99		98	97	97
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82
5	96	89	84	80		94	88	83	79		86	82	79		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	78	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	70		77	73	70		76	72	70
8	84	76	71	67		83	76	71	67		75	70	67		74	69	66		73	69	66
9	81	73	67	64		80	72	67	64		71	67	63		70	66	63		70	66	63
10	78	69	64	61		77	69	64	61		68	64	60		67	63	60		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226451
5°	220426
10°	210350
15°	190421
20°	164748
25°	135129
30°	77632
35°	24119
40°	6469
45°	2264
50°	546
55°	191
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2264 cd/sqm

TEST NUMBER: P1266759

CATALOG NUMBER: P3A05R509735DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.8	14.5
10°-20°	232.4	35.9
20°-30°	244.3	37.7
30°-40°	69.9	10.8
40°-50°	6.8	1.1
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.5	88.0
0°-40°	640.4	98.8
0°-60°	647.8	100.0
0°-90°	648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	648.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1033	
5°	1001	94
15°	839	232
25°	558	244
35°	90	70
45°	7	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266759

CATALOG NUMBER: P3A05R509735DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1032.7
1°	1031.1
2°	1026.5
3°	1019.9
4°	1011.0
5°	1001.4
6°	991.1
7°	980.1
8°	969.8
9°	957.9
10°	944.7
11°	929.4
12°	911.8
13°	889.8
14°	866.0
15°	838.8
16°	810.0
17°	782.1
18°	753.5
19°	728.4
20°	706.0
21°	684.5
22°	660.0
23°	631.9
24°	599.0
25°	558.5
26°	514.6
27°	465.7
28°	417.0
29°	364.4
30°	306.6
31°	252.4
32°	202.6
32.5°	180.8
33°	158.9
34°	121.9
35°	90.1
36°	66.1
37°	49.2
37.5°	42.5
38°	36.8
39°	28.6
40°	22.6
42.5°	12.8
45°	7.3



TEST NUMBER: P1266759
CATALOG NUMBER: P3A05R509735DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.1
50°	1.6
52.5°	0.7
55°	0.5
57.5°	0.5
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)