

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266837

Luminaire Tested: P3A05R609735DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R609735DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 339.0 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266837
CATALOG NUMBER: P3A05R609735DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266837

CATALOG NUMBER: P3A05R609735DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85914
5°	83975
10°	78622
15°	70534
20°	60672
25°	50156
30°	39626
35°	29419
40°	20267
45°	12714
50°	6993
55°	4091
60°	3684
65°	3165
70°	2693
75°	2796
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12714 cd/sqm



TEST NUMBER: P1266837
 CATALOG NUMBER: P3A05R609735DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.5	10.5
10°-20°	86.3	25.5
20°-30°	94.7	27.9
30°-40°	69.0	20.3
40°-50°	32.6	9.6
50°-60°	10.7	3.1
60°-70°	6.1	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.5	63.9
0°-40°	285.4	84.2
0°-60°	328.7	97.0
0°-90°	339.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	339.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	392	
5°	382	36
15°	311	86
25°	207	95
35°	110	69
45°	41	33
55°	11	11
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1266837
CATALOG NUMBER: P3A05R609735DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	391.8
2.5°	389.5
5°	381.5
7.5°	369.4
10°	353.1
12.5°	333.6
15°	310.7
17.5°	286.0
20°	260.0
22.5°	233.4
25°	207.3
27.5°	181.2
30°	156.5
32.5°	132.8
35°	109.9
37.5°	89.4
40°	70.8
42.5°	54.5
45°	41.0
47.5°	29.8
50°	20.5
52.5°	13.5
55°	10.7
57.5°	9.3
60°	8.4
62.5°	7.0
65°	6.1
67.5°	5.1
70°	4.2
72.5°	3.7
75°	3.3
77.5°	2.3
80°	1.9
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)