

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264798

Luminaire Tested: P3A09R559730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R559730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 272.0 lumens
Efficiency: N/A
Efficacy: 24.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264798
CATALOG NUMBER: P3A09R559730DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264798
 CATALOG NUMBER: P3A09R559730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51136
5°	50495
10°	48496
15°	45358
20°	41374
25°	36921
30°	32283
35°	26823
40°	21154
45°	14358
50°	8767
55°	4549
60°	4210
65°	3995
70°	3719
75°	3304
80°	3283
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14358 cd/sqm



TEST NUMBER: P1264798
 CATALOG NUMBER: P3A09R559730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.5	7.9
10°-20°	55.8	20.5
20°-30°	69.9	25.7
30°-40°	62.4	22.9
40°-50°	36.6	13.4
50°-60°	12.6	4.6
60°-70°	7.6	2.8
70°-80°	4.2	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	147.3	54.2
0°-40°	209.7	77.1
0°-60°	258.9	95.2
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	233	
5°	229	22
15°	200	56
25°	153	70
35°	100	62
45°	46	37
55°	12	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1264798
CATALOG NUMBER: P3A09R559730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	233.2
2.5°	231.9
5°	229.4
7.5°	224.2
10°	217.8
12.5°	209.8
15°	199.8
17.5°	189.2
20°	177.3
22.5°	165.1
25°	152.6
27.5°	140.1
30°	127.5
32.5°	114.0
35°	100.2
37.5°	86.7
40°	73.9
42.5°	60.1
45°	46.3
47.5°	35.3
50°	25.7
52.5°	16.7
55°	11.9
57.5°	10.6
60°	9.6
62.5°	8.7
65°	7.7
67.5°	6.7
70°	5.8
72.5°	4.8
75°	3.9
77.5°	3.2
80°	2.6
82.5°	1.6
85°	1.0
87.5°	0.6
90°	0.0

(END OF REPORT)