

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264814

Luminaire Tested: P3A09R609730DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R609730DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 848.1 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264814

CATALOG NUMBER: P3A09R609730DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1264814

CATALOG NUMBER: P3A09R609730DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	68	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202506
5°	194475
10°	200219
15°	202793
20°	179076
25°	150904
30°	122399
35°	79719
40°	36611
45°	14048
50°	4708
55°	1262
60°	1140
65°	1038
70°	833
75°	1101
80°	884
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14048 cd/sqm

TEST NUMBER: P1264814

CATALOG NUMBER: P3A09R609730DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	10.0
10°-20°	244.6	28.8
20°-30°	285.3	33.6
30°-40°	184.1	21.7
40°-50°	41.3	4.9
50°-60°	4.1	0.5
60°-70°	2.0	0.2
70°-80°	1.1	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	615.0	72.5
0°-40°	799.1	94.2
0°-60°	844.5	99.6
0°-90°	848.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	924	
5°	884	85
15°	893	245
25°	624	285
35°	298	184
45°	45	41
55°	3	4
65°	2	2
75°	1	1
85°	1	0
90°	0	

TEST NUMBER: P1264814

CATALOG NUMBER: P3A09R609730DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	923.5
2.5°	908.4
5°	883.5
7.5°	882.1
10°	899.2
12.5°	910.3
15°	893.3
17.5°	842.1
20°	767.4
22.5°	689.3
25°	623.7
27.5°	559.5
30°	483.4
32.5°	394.2
35°	297.8
37.5°	203.3
40°	127.9
42.5°	76.7
45°	45.3
47.5°	26.2
50°	13.8
52.5°	4.6
55°	3.3
57.5°	2.6
60°	2.6
62.5°	2.0
65°	2.0
67.5°	2.0
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)