

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264888

Luminaire Tested: P3A09R709730DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264888  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R709730DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 472.0 lumens  
Efficiency: N/A  
Efficacy: 42.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264888  
CATALOG NUMBER: P3A09R709730DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264888

CATALOG NUMBER: P3A09R709730DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	110715
5°	108672
10°	102470
15°	93008
20°	81347
25°	68617
30°	56186
35°	43580
40°	31201
45°	19754
50°	9859
55°	6040
60°	5175
65°	4774
70°	4231
75°	3897
80°	3283
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19754 cd/sqm



TEST NUMBER: P1264888

CATALOG NUMBER: P3A09R709730DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.1	9.8
10°-20°	114.0	24.2
20°-30°	129.8	27.5
30°-40°	101.5	21.5
40°-50°	49.9	10.6
50°-60°	15.3	3.2
60°-70°	9.1	1.9
70°-80°	4.9	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.9	61.4
0°-40°	391.4	82.9
0°-60°	456.6	96.7
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	505	
5°	494	46
15°	410	114
25°	284	130
35°	163	102
45°	64	50
55°	16	15
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1264888  
CATALOG NUMBER: P3A09R709730DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	504.9
2.5°	502.3
5°	493.7
7.5°	479.9
10°	460.2
12.5°	437.3
15°	409.7
17.5°	380.1
20°	348.6
22.5°	315.8
25°	283.6
27.5°	252.1
30°	221.9
32.5°	191.7
35°	162.8
37.5°	135.3
40°	109.0
42.5°	84.7
45°	63.7
47.5°	44.6
50°	28.9
52.5°	19.0
55°	15.8
57.5°	13.8
60°	11.8
62.5°	10.5
65°	9.2
67.5°	7.9
70°	6.6
72.5°	5.3
75°	4.6
77.5°	3.9
80°	2.6
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)