

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266961

Luminaire Tested: P3A09R209735DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1266961  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R209735DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 861.1 lumens  
Efficiency: N/A  
Efficacy: 77.6 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266961

CATALOG NUMBER: P3A09R209735DE010 E3CB1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1266961

CATALOG NUMBER: P3A09R209735DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 110 | 113 | 112 | 110 | 109 | 108 | 106 | 105 |  | 104 | 103 | 102 |  | 101 |
| 2   | 112 | 109 | 106 | 104 | 110 | 108 | 105 | 103 | 104 | 103 | 101 |  | 102 | 100 | 99  |  | 99  |
| 3   | 109 | 105 | 102 | 100 | 108 | 104 | 101 | 99  | 102 | 99  | 97  |  | 99  | 98  | 96  |  | 97  |
| 4   | 107 | 102 | 99  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 94  |  | 97  | 95  | 93  |  | 96  |
| 5   | 104 | 99  | 96  | 93  | 103 | 98  | 95  | 93  | 97  | 94  | 92  |  | 95  | 93  | 91  |  | 94  |
| 6   | 102 | 97  | 93  | 91  | 101 | 96  | 93  | 90  | 95  | 92  | 90  |  | 94  | 91  | 89  |  | 93  |
| 7   | 100 | 94  | 91  | 88  | 99  | 94  | 91  | 88  | 93  | 90  | 88  |  | 92  | 89  | 87  |  | 91  |
| 8   | 98  | 92  | 89  | 86  | 97  | 92  | 89  | 86  | 91  | 88  | 86  |  | 90  | 88  | 86  |  | 89  |
| 9   | 96  | 90  | 87  | 85  | 95  | 90  | 87  | 85  | 89  | 86  | 84  |  | 89  | 86  | 84  |  | 88  |
| 10  | 94  | 89  | 85  | 83  | 93  | 88  | 85  | 83  | 88  | 85  | 83  |  | 87  | 84  | 83  |  | 86  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1337239 |
| 5°  | 1160662 |
| 10° | 717177  |
| 15° | 249105  |
| 20° | 76493   |
| 25° | 27050   |
| 30° | 10002   |
| 35° | 4015    |
| 40° | 2147    |
| 45° | 837     |
| 50° | 478     |
| 55° | 535     |
| 60° | 614     |
| 65° | 363     |
| 70° | 449     |
| 75° | 593     |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 837 cd/sqm

TEST NUMBER: P1266961

CATALOG NUMBER: P3A09R209735DE010 E3CB1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 437.6  | 50.8      |
| 10°-20°   | 347.2  | 40.3      |
| 20°-30°   | 60.1   | 7.0       |
| 30°-40°   | 10.9   | 1.3       |
| 40°-50°   | 2.5    | 0.3       |
| 50°-60°   | 1.3    | 0.1       |
| 60°-70°   | 0.8    | 0.1       |
| 70°-80°   | 0.6    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 845.0  | 98.1      |
| 0°-40°    | 855.9  | 99.4      |
| 0°-60°    | 859.7  | 99.8      |
| 0°-90°    | 861.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 861.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6098 |      |
| 5°  | 5273 | 438  |
| 15° | 1097 | 347  |
| 25° | 112  | 60   |
| 35° | 15   | 11   |
| 45° | 3    | 3    |
| 55° | 1    | 1    |
| 65° | 1    | 1    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1266961

CATALOG NUMBER: P3A09R209735DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 6098.3 |
| 1°    | 6069.0 |
| 2°    | 5953.1 |
| 3°    | 5767.0 |
| 4°    | 5549.0 |
| 5°    | 5272.9 |
| 6°    | 4956.7 |
| 7°    | 4588.7 |
| 8°    | 4169.6 |
| 9°    | 3698.6 |
| 10°   | 3220.9 |
| 12.5° | 2031.6 |
| 15°   | 1097.3 |
| 17.5° | 586.1  |
| 20°   | 327.8  |
| 22.5° | 187.4  |
| 25°   | 111.8  |
| 27.5° | 68.2   |
| 30°   | 39.5   |
| 32.5° | 23.2   |
| 35°   | 15.0   |
| 37.5° | 10.2   |
| 40°   | 7.5    |
| 42.5° | 4.8    |
| 45°   | 2.7    |
| 47.5° | 1.4    |
| 50°   | 1.4    |
| 52.5° | 1.4    |
| 55°   | 1.4    |
| 57.5° | 1.4    |
| 60°   | 1.4    |
| 62.5° | 0.7    |
| 65°   | 0.7    |
| 67.5° | 0.7    |
| 70°   | 0.7    |
| 72.5° | 0.7    |
| 75°   | 0.7    |
| 77.5° | 0.7    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)