

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267068

Luminaire Tested: P3A09R359735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R359735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 217.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267068
CATALOG NUMBER: P3A09R359735DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1267068

CATALOG NUMBER: P3A09R359735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80				80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57				57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69753
5°	68039
10°	62190
15°	52781
20°	41794
25°	31599
30°	23016
35°	15553
40°	9561
45°	5489
50°	3309
55°	2676
60°	2324
65°	2075
70°	1731
75°	1694
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5489 cd/sqm



TEST NUMBER: P1267068

CATALOG NUMBER: P3A09R359735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.6	13.2
10°-20°	64.1	29.5
20°-30°	60.0	27.6
30°-40°	36.7	16.9
40°-50°	14.5	6.7
50°-60°	6.4	2.9
60°-70°	4.0	1.8
70°-80°	2.1	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	152.6	70.4
0°-40°	189.3	87.3
0°-60°	210.2	96.9
0°-90°	217.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	217.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	318	
5°	309	29
15°	232	64
25°	131	60
35°	58	37
45°	18	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1267068

CATALOG NUMBER: P3A09R359735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	318.1
1°	318.4
2°	317.4
3°	315.4
4°	312.4
5°	309.1
6°	304.7
7°	299.7
8°	293.7
9°	287.0
10°	279.3
11°	271.3
12°	262.6
13°	253.3
14°	242.9
15°	232.5
17.5°	205.8
20°	179.1
22.5°	153.4
25°	130.6
27.5°	109.6
30°	90.9
32.5°	73.5
35°	58.1
37.5°	44.4
40°	33.4
42.5°	24.1
45°	17.7
47.5°	12.7
50°	9.7
52.5°	8.0
55°	7.0
57.5°	6.0
60°	5.3
62.5°	4.7
65°	4.0
67.5°	3.3
70°	2.7
72.5°	2.3
75°	2.0
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3



TEST NUMBER: P1267068
CATALOG NUMBER: P3A09R359735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)