

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267113

Luminaire Tested: P3A09R459735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R459735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 374.0 lumens
Efficiency: N/A
Efficacy: 33.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267113

CATALOG NUMBER: P3A09R459735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267113

CATALOG NUMBER: P3A09R459735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140449
5°	137156
10°	126094
15°	106834
20°	82887
25°	57947
30°	36512
35°	21496
40°	12166
45°	5923
50°	2047
55°	1644
60°	1623
65°	1557
70°	1475
75°	1440
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5923 cd/sqm

TEST NUMBER: P1267113

CATALOG NUMBER: P3A09R459735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	15.4
10°-20°	129.2	34.6
20°-30°	109.7	29.3
30°-40°	52.4	14.0
40°-50°	15.8	4.2
50°-60°	4.0	1.1
60°-70°	3.0	0.8
70°-80°	1.8	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.6	79.3
0°-40°	349.0	93.3
0°-60°	368.8	98.6
0°-90°	374.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	374.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	640	
5°	623	58
15°	471	129
25°	240	110
35°	80	52
45°	19	16
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1267113

CATALOG NUMBER: P3A09R459735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	640.5
2.5°	636.5
5°	623.1
7.5°	600.0
10°	566.3
12.5°	521.4
15°	470.6
17.5°	414.1
20°	355.2
22.5°	295.3
25°	239.5
27.5°	188.6
30°	144.2
32.5°	108.4
35°	80.3
37.5°	59.2
40°	42.5
42.5°	29.4
45°	19.1
47.5°	10.7
50°	6.0
52.5°	4.7
55°	4.3
57.5°	4.0
60°	3.7
62.5°	3.3
65°	3.0
67.5°	2.7
70°	2.3
72.5°	2.0
75°	1.7
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)