

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267142

Luminaire Tested: P3A09R509735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R509735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 375.9 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267142
CATALOG NUMBER: P3A09R509735DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1267142
 CATALOG NUMBER: P3A09R509735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76				76
5	93	85	80	76	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	68				68
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64				64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60				60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57				57
10	74	65	59	56	73	65	59	56	64	59	55	63	59	55	62	58	55	54				54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119705
5°	117301
10°	109862
15°	98366
20°	82771
25°	63173
30°	41044
35°	24333
40°	14055
45°	7039
50°	2627
55°	2026
60°	1886
65°	1712
70°	1731
75°	1694
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7039 cd/sqm



TEST NUMBER: P1267142
 CATALOG NUMBER: P3A09R509735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	13.2
10°-20°	119.8	31.9
20°-30°	117.5	31.3
30°-40°	59.2	15.7
40°-50°	18.7	5.0
50°-60°	4.8	1.3
60°-70°	3.4	0.9
70°-80°	2.1	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.9	76.3
0°-40°	346.1	92.1
0°-60°	369.7	98.3
0°-90°	375.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	375.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	546	
5°	533	50
15°	433	120
25°	261	118
35°	91	59
45°	23	19
55°	5	5
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1267142
CATALOG NUMBER: P3A09R509735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	545.9
2.5°	542.6
5°	532.9
7.5°	515.5
10°	493.4
12.5°	465.0
15°	433.3
17.5°	396.5
20°	354.7
22.5°	309.6
25°	261.1
27.5°	209.6
30°	162.1
32.5°	122.0
35°	90.9
37.5°	67.2
40°	49.1
42.5°	34.8
45°	22.7
47.5°	13.0
50°	7.7
52.5°	5.7
55°	5.3
57.5°	4.7
60°	4.3
62.5°	4.0
65°	3.3
67.5°	3.0
70°	2.7
72.5°	2.3
75°	2.0
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)