

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267221

Luminaire Tested: P3A09R659735DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R659735DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 843.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267221

CATALOG NUMBER: P3A09R659735DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1267221

CATALOG NUMBER: P3A09R659735DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95	94
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89	87
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83	81
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77	75
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72	70
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67	66
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63	62
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59	58
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56	54
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206014
5°	193902
10°	191424
15°	188060
20°	177559
25°	164792
30°	128096
35°	74097
40°	29856
45°	13738
50°	5356
55°	2103
60°	1798
65°	1764
70°	1731
75°	1694
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13738 cd/sqm

TEST NUMBER: P1267221

CATALOG NUMBER: P3A09R659735DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	9.9
10°-20°	231.3	27.4
20°-30°	302.8	35.9
30°-40°	175.4	20.8
40°-50°	37.5	4.5
50°-60°	6.1	0.7
60°-70°	3.4	0.4
70°-80°	2.0	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.9	73.3
0°-40°	793.3	94.1
0°-60°	836.9	99.3
0°-90°	843.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	940	
5°	881	84
15°	828	231
25°	681	303
35°	277	175
45°	44	38
55°	6	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1267221

CATALOG NUMBER: P3A09R659735DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	939.5
2.5°	912.9
5°	880.9
7.5°	867.9
10°	859.7
12.5°	848.1
15°	828.4
17.5°	797.7
20°	760.9
22.5°	726.1
25°	681.1
27.5°	605.4
30°	505.9
32.5°	392.0
35°	276.8
37.5°	175.2
40°	104.3
42.5°	65.5
45°	44.3
47.5°	28.6
50°	15.7
52.5°	7.5
55°	5.5
57.5°	4.8
60°	4.1
62.5°	4.1
65°	3.4
67.5°	2.7
70°	2.7
72.5°	2.0
75°	2.0
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)