

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267447

Luminaire Tested: P3A13R309735DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R309735DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 738.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267447
CATALOG NUMBER: P3A13R309735DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267447
 CATALOG NUMBER: P3A13R309735DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174350
5°	170438
10°	158492
15°	141022
20°	121297
25°	102756
30°	85304
35°	66896
40°	47947
45°	31445
50°	17910
55°	11775
60°	11139
65°	10325
70°	9296
75°	8472
80°	7956
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31445 cd/sqm



TEST NUMBER: P1267447
 CATALOG NUMBER: P3A13R309735DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	9.7
10°-20°	172.7	23.4
20°-30°	194.6	26.4
30°-40°	155.4	21.1
40°-50°	79.9	10.8
50°-60°	30.1	4.1
60°-70°	19.7	2.7
70°-80°	10.7	1.4
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.2	59.5
0°-40°	594.6	80.6
0°-60°	704.6	95.5
0°-90°	738.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	738.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	795	
5°	774	72
15°	621	173
25°	425	195
35°	250	155
45°	101	80
55°	31	30
65°	20	20
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P1267447
CATALOG NUMBER: P3A13R309735DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	795.1
1°	795.1
2°	792.4
3°	787.9
4°	781.5
5°	774.3
6°	765.2
7°	753.5
8°	740.8
9°	726.3
10°	711.8
11°	695.5
12°	678.3
13°	660.2
14°	641.2
15°	621.2
17.5°	570.5
20°	519.8
22.5°	470.9
25°	424.7
27.5°	379.4
30°	336.9
32.5°	293.4
35°	249.9
37.5°	207.4
40°	167.5
42.5°	132.2
45°	101.4
47.5°	75.2
50°	52.5
52.5°	37.1
55°	30.8
57.5°	28.1
60°	25.4
62.5°	22.6
65°	19.9
67.5°	17.2
70°	14.5
72.5°	11.8
75°	10.0
77.5°	8.2
80°	6.3
82.5°	4.5
85°	2.7
87.5°	0.9



TEST NUMBER: P1267447
CATALOG NUMBER: P3A13R309735DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)