

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269728

Luminaire Tested: P3A13R159740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R159740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 479.0 lumens
Efficiency: N/A
Efficacy: 32.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269728

CATALOG NUMBER: P3A13R159740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269728

CATALOG NUMBER: P3A13R159740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	409200
5°	363217
10°	252233
15°	149172
20°	84964
25°	48559
30°	26865
35°	14322
40°	7929
45°	4280
50°	2661
55°	2103
60°	1842
65°	1660
70°	1475
75°	1525
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4280 cd/sqm

TEST NUMBER: P1269728

CATALOG NUMBER: P3A13R159740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.3	29.3
10°-20°	185.2	38.7
20°-30°	95.4	19.9
30°-40°	35.8	7.5
40°-50°	11.7	2.4
50°-60°	5.0	1.1
60°-70°	3.2	0.7
70°-80°	1.9	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.9	87.9
0°-40°	456.7	95.3
0°-60°	473.4	98.8
0°-90°	479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1866	
5°	1650	140
15°	657	185
25°	201	95
35°	54	36
45°	14	12
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1269728

CATALOG NUMBER: P3A13R159740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1866.1
1°	1862.4
2°	1837.9
3°	1791.3
4°	1729.9
5°	1650.1
6°	1559.7
7°	1460.5
8°	1350.2
9°	1241.3
10°	1132.8
12.5°	871.7
15°	657.1
17.5°	491.9
20°	364.1
22.5°	271.8
25°	200.7
27.5°	146.3
30°	106.1
32.5°	75.2
35°	53.5
37.5°	38.3
40°	27.7
42.5°	19.8
45°	13.8
47.5°	10.2
50°	7.8
52.5°	6.5
55°	5.5
57.5°	4.6
60°	4.2
62.5°	3.7
65°	3.2
67.5°	2.8
70°	2.3
72.5°	2.3
75°	1.8
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)