

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269748

Luminaire Tested: P3A13R159740DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1269748  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R159740DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 439.0 lumens  
Efficiency: N/A  
Efficacy: 30.1 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269748

CATALOG NUMBER: P3A13R159740DE010 E3PHLP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1269748

CATALOG NUMBER: P3A13R159740DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99  | 97  |  | 98  | 96  | 94  |  | 95  |
| 2   | 105 | 99  | 94  | 90  | 102 | 97  | 92  | 89  | 94  | 90  | 87  |  | 91  | 87  | 85  |  | 88  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 71  |  | 79  | 74  | 71  |  | 77  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 67  | 62  | 82  | 73  | 66  | 62  | 71  | 65  | 61  |  | 70  | 65  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 61  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  |
| 10  | 69  | 59  | 52  | 48  | 68  | 58  | 52  | 48  | 57  | 52  | 48  |  | 56  | 51  | 48  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 164307 |
| 5°  | 150869 |
| 10° | 120216 |
| 15° | 89830  |
| 20° | 68233  |
| 25° | 51656  |
| 30° | 38234  |
| 35° | 27305  |
| 40° | 18692  |
| 45° | 13087  |
| 50° | 11121  |
| 55° | 10934  |
| 60° | 11315  |
| 65° | 11986  |
| 70° | 12182  |
| 75° | 12709  |
| 80° | 13764  |
| 85° | 13586  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 15960 cd/sqm

TEST NUMBER: P1269748

CATALOG NUMBER: P3A13R159740DE010 E3PHLP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 60.7   | 13.8      |
| 10°-20°   | 111.0  | 25.3      |
| 20°-30°   | 98.3   | 22.4      |
| 30°-40°   | 64.4   | 14.7      |
| 40°-50°   | 34.4   | 7.8       |
| 50°-60°   | 26.0   | 5.9       |
| 60°-70°   | 22.4   | 5.1       |
| 70°-80°   | 15.4   | 3.5       |
| 80°-90°   | 6.3    | 1.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 270.0  | 61.5      |
| 0°-40°    | 334.5  | 76.2      |
| 0°-60°    | 394.9  | 90.0      |
| 0°-90°    | 439.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 439.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 749 |      |
| 5°  | 685 | 61   |
| 15° | 396 | 111  |
| 25° | 214 | 98   |
| 35° | 102 | 64   |
| 45° | 42  | 34   |
| 55° | 29  | 26   |
| 65° | 23  | 22   |
| 75° | 15  | 15   |
| 85° | 5   | 6    |
| 90° | 0   |      |

TEST NUMBER: P1269748

CATALOG NUMBER: P3A13R159740DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 749.3 |
| 2.5°  | 731.6 |
| 5°    | 685.4 |
| 7.5°  | 617.4 |
| 10°   | 539.9 |
| 12.5° | 465.1 |
| 15°   | 395.7 |
| 17.5° | 340.0 |
| 20°   | 292.4 |
| 22.5° | 250.2 |
| 25°   | 213.5 |
| 27.5° | 180.9 |
| 30°   | 151.0 |
| 32.5° | 125.1 |
| 35°   | 102.0 |
| 37.5° | 81.6  |
| 40°   | 65.3  |
| 42.5° | 51.7  |
| 45°   | 42.2  |
| 47.5° | 36.7  |
| 50°   | 32.6  |
| 52.5° | 31.3  |
| 55°   | 28.6  |
| 57.5° | 27.2  |
| 60°   | 25.8  |
| 62.5° | 24.5  |
| 65°   | 23.1  |
| 67.5° | 20.4  |
| 70°   | 19.0  |
| 72.5° | 16.3  |
| 75°   | 15.0  |
| 77.5° | 12.2  |
| 80°   | 10.9  |
| 82.5° | 9.5   |
| 85°   | 5.4   |
| 87.5° | 2.7   |
| 90°   | 0.0   |

(END OF REPORT)