

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267468

Luminaire Tested: P3A13R359735DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267468  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R359735DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 952.0 lumens  
Efficiency: N/A  
Efficacy: 65.2 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267468  
CATALOG NUMBER: P3A13R359735DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1267468

CATALOG NUMBER: P3A13R359735DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	480137
5°	461456
10°	402063
15°	307947
20°	206028
25°	124677
30°	71530
35°	39993
40°	21268
45°	10947
50°	5254
55°	4167
60°	3991
65°	3269
70°	3462
75°	3050
80°	3410
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10947 cd/sqm



TEST NUMBER: P1267468  
 CATALOG NUMBER: P3A13R359735DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	190.7	20.0
10°-20°	369.6	38.8
20°-30°	242.0	25.4
30°-40°	98.2	10.3
40°-50°	29.4	3.1
50°-60°	10.0	1.1
60°-70°	6.7	0.7
70°-80°	3.9	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.4	84.3
0°-40°	900.5	94.6
0°-60°	940.0	98.7
0°-90°	952.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2190	
5°	2096	191
15°	1356	370
25°	515	242
35°	149	98
45°	35	29
55°	11	10
65°	6	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1267468  
CATALOG NUMBER: P3A13R359735DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2189.6
1°	2186.0
2°	2176.1
3°	2156.1
4°	2132.6
5°	2096.4
6°	2051.1
7°	2000.4
8°	1943.3
9°	1878.1
10°	1805.7
11°	1725.1
12°	1640.9
13°	1546.7
14°	1457.0
15°	1356.5
17.5°	1112.9
20°	882.9
22.5°	679.2
25°	515.3
27.5°	384.0
30°	282.5
32.5°	207.4
35°	149.4
37.5°	106.0
40°	74.3
42.5°	51.6
45°	35.3
47.5°	23.5
50°	15.4
52.5°	11.8
55°	10.9
57.5°	10.0
60°	9.1
62.5°	8.2
65°	6.3
67.5°	5.4
70°	5.4
72.5°	4.5
75°	3.6
77.5°	2.7
80°	2.7
82.5°	1.8
85°	0.9
87.5°	0.9



TEST NUMBER: P1267468  
CATALOG NUMBER: P3A13R359735DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)