

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269871

Luminaire Tested: P3A13R409740DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409740DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1322.9 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269871
CATALOG NUMBER: P3A13R409740DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1269871

CATALOG NUMBER: P3A13R409740DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	94	94	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	82	79	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	80	77	75	73
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	696589
5°	693241
10°	670640
15°	593352
20°	387134
25°	137137
30°	29093
35°	9583
40°	3492
45°	1178
50°	955
55°	1070
60°	833
65°	986
70°	577
75°	763
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 1512 cd/sqm



TEST NUMBER: P1269871
 CATALOG NUMBER: P3A13R409740DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.3	22.4
10°-20°	690.1	52.2
20°-30°	299.5	22.6
30°-40°	27.6	2.1
40°-50°	3.9	0.3
50°-60°	2.4	0.2
60°-70°	1.8	0.1
70°-80°	1.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1285.9	97.2
0°-40°	1313.5	99.3
0°-60°	1319.9	99.8
0°-90°	1322.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1322.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3177	
5°	3149	296
15°	2614	690
25°	567	299
35°	36	28
45°	4	4
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1269871
CATALOG NUMBER: P3A13R409740DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3176.7
2.5°	3173.0
5°	3149.4
7.5°	3099.5
10°	3011.9
12.5°	2864.1
15°	2613.7
17.5°	2198.5
20°	1659.0
22.5°	1077.1
25°	566.8
27.5°	243.9
30°	114.9
32.5°	62.1
35°	35.8
37.5°	21.7
40°	12.2
42.5°	6.6
45°	3.8
47.5°	2.8
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.8
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)