

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267754

Luminaire Tested: P3A17R259735DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R259735DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1256.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267754

CATALOG NUMBER: P3A17R259735DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1267754

CATALOG NUMBER: P3A17R259735DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	805681
5°	751682
10°	602149
15°	408742
20°	247332
25°	144637
30°	82367
35°	45294
40°	24045
45°	12652
50°	7369
55°	5505
60°	4736
65°	4981
70°	4616
75°	4067
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12652 cd/sqm

TEST NUMBER: P1267754

CATALOG NUMBER: P3A17R259735DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.0	24.1
10°-20°	495.0	39.4
20°-30°	282.9	22.5
30°-40°	111.6	8.9
40°-50°	34.2	2.7
50°-60°	13.5	1.1
60°-70°	9.1	0.7
70°-80°	5.1	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.9	86.1
0°-40°	1192.5	94.9
0°-60°	1240.2	98.7
0°-90°	1256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3674	
5°	3415	303
15°	1800	495
25°	598	283
35°	169	112
45°	41	34
55°	14	14
65°	10	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1267754

CATALOG NUMBER: P3A17R259735DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3674.2
1°	3667.0
2°	3637.0
3°	3584.2
4°	3510.9
5°	3414.9
6°	3302.1
7°	3174.8
8°	3027.2
9°	2876.0
10°	2704.3
11°	2535.1
12°	2349.0
13°	2165.4
14°	1976.9
15°	1800.5
17.5°	1396.0
20°	1059.9
22.5°	795.8
25°	597.8
27.5°	442.9
30°	325.3
32.5°	235.3
35°	169.2
37.5°	120.0
40°	84.0
42.5°	57.6
45°	40.8
47.5°	28.8
50°	21.6
52.5°	16.8
55°	14.4
57.5°	13.2
60°	10.8
62.5°	9.6
65°	9.6
67.5°	8.4
70°	7.2
72.5°	6.0
75°	4.8
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2



TEST NUMBER: P1267754

CATALOG NUMBER: P3A17R259735DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)