

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270005

Luminaire Tested: P3A13R609740DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1270005  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R609740DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 685.0 lumens  
Efficiency: N/A  
Efficacy: 46.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270005

CATALOG NUMBER: P3A13R609740DE010 E3DLP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1270005

CATALOG NUMBER: P3A13R609740DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  |  | 93  | 91  | 88  |  | 91  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  |  | 87  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 77  | 93  | 86  | 80  | 76  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 80  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 60  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  |  | 57  | 52  | 49  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 173605 |
| 5°  | 169711 |
| 10° | 158870 |
| 15° | 142543 |
| 20° | 122581 |
| 25° | 101353 |
| 30° | 80088  |
| 35° | 59481  |
| 40° | 40962  |
| 45° | 25677  |
| 50° | 14123  |
| 55° | 8296   |
| 60° | 7412   |
| 65° | 6330   |
| 70° | 5450   |
| 75° | 5592   |
| 80° | 4799   |
| 85° | 4780   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25677 cd/sqm

TEST NUMBER: P1270005

CATALOG NUMBER: P3A13R609740DE010 E3DLP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 71.8   | 10.5      |
| 10°-20°   | 174.4  | 25.5      |
| 20°-30°   | 191.3  | 27.9      |
| 30°-40°   | 139.4  | 20.3      |
| 40°-50°   | 65.8   | 9.6       |
| 50°-60°   | 21.6   | 3.1       |
| 60°-70°   | 12.2   | 1.8       |
| 70°-80°   | 6.6    | 1.0       |
| 80°-90°   | 2.0    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 437.4  | 63.9      |
| 0°-40°    | 576.8  | 84.2      |
| 0°-60°    | 664.1  | 97.0      |
| 0°-90°    | 685.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 685.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 792 |      |
| 5°  | 771 | 72   |
| 15° | 628 | 174  |
| 25° | 419 | 191  |
| 35° | 222 | 139  |
| 45° | 83  | 66   |
| 55° | 22  | 22   |
| 65° | 12  | 12   |
| 75° | 7   | 7    |
| 85° | 2   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1270005

CATALOG NUMBER: P3A13R609740DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 791.7 |
| 2.5°  | 787.0 |
| 5°    | 771.0 |
| 7.5°  | 746.5 |
| 10°   | 713.5 |
| 12.5° | 674.0 |
| 15°   | 627.9 |
| 17.5° | 578.0 |
| 20°   | 525.3 |
| 22.5° | 471.6 |
| 25°   | 418.9 |
| 27.5° | 366.2 |
| 30°   | 316.3 |
| 32.5° | 268.3 |
| 35°   | 222.2 |
| 37.5° | 180.7 |
| 40°   | 143.1 |
| 42.5° | 110.1 |
| 45°   | 82.8  |
| 47.5° | 60.2  |
| 50°   | 41.4  |
| 52.5° | 27.3  |
| 55°   | 21.7  |
| 57.5° | 18.8  |
| 60°   | 16.9  |
| 62.5° | 14.1  |
| 65°   | 12.2  |
| 67.5° | 10.4  |
| 70°   | 8.5   |
| 72.5° | 7.5   |
| 75°   | 6.6   |
| 77.5° | 4.7   |
| 80°   | 3.8   |
| 82.5° | 2.8   |
| 85°   | 1.9   |
| 87.5° | 0.9   |
| 90°   | 0.0   |

(END OF REPORT)