

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267874

Luminaire Tested: P3A17R459735DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R459735DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1341.0 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267874

CATALOG NUMBER: P3A17R459735DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267874

CATALOG NUMBER: P3A17R459735DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	503600
5°	491788
10°	452074
15°	383044
20°	297199
25°	207762
30°	130881
35°	77042
40°	43596
45°	21212
50°	7369
55°	5964
60°	5789
65°	5604
70°	5386
75°	5083
80°	4546
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21212 cd/sqm

TEST NUMBER: P1267874

CATALOG NUMBER: P3A17R459735DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.8	15.4
10°-20°	463.4	34.6
20°-30°	393.5	29.3
30°-40°	187.7	14.0
40°-50°	56.5	4.2
50°-60°	14.3	1.1
60°-70°	10.7	0.8
70°-80°	6.3	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1063.6	79.3
0°-40°	1251.3	93.3
0°-60°	1322.2	98.6
0°-90°	1341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1341.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2297	
5°	2234	207
15°	1687	463
25°	859	393
35°	288	188
45°	68	57
55°	16	14
65°	11	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1267874

CATALOG NUMBER: P3A17R459735DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2296.6
2.5°	2282.2
5°	2234.2
7.5°	2151.5
10°	2030.3
12.5°	1869.6
15°	1687.3
17.5°	1484.7
20°	1273.6
22.5°	1058.9
25°	858.7
27.5°	676.4
30°	516.9
32.5°	388.6
35°	287.8
37.5°	212.3
40°	152.3
42.5°	105.5
45°	68.4
47.5°	38.4
50°	21.6
52.5°	16.8
55°	15.6
57.5°	14.4
60°	13.2
62.5°	12.0
65°	10.8
67.5°	9.6
70°	8.4
72.5°	7.2
75°	6.0
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)