

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270121

Luminaire Tested: P3A17R259740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R259740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1587.9 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270121
CATALOG NUMBER: P3A17R259740DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1270121

CATALOG NUMBER: P3A17R259740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1697803
5°	1574660
10°	1221175
15°	612330
20°	201174
25°	79988
30°	30005
35°	8673
40°	3922
45°	1551
50°	1262
55°	956
60°	1096
65°	1297
70°	769
75°	1017
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1551 cd/sqm



TEST NUMBER: P1270121
 CATALOG NUMBER: P3A17R259740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	629.2	39.6
10°-20°	750.7	47.3
20°-30°	169.2	10.7
30°-40°	27.4	1.7
40°-50°	4.9	0.3
50°-60°	2.6	0.2
60°-70°	2.3	0.1
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1549.1	97.6
0°-40°	1576.6	99.3
0°-60°	1584.1	99.8
0°-90°	1587.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1587.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7743	
5°	7154	629
15°	2697	751
25°	331	169
35°	32	27
45°	5	5
55°	2	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1270121
CATALOG NUMBER: P3A17R259740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7742.6
1°	7730.1
2°	7667.7
3°	7553.0
4°	7379.5
5°	7153.7
6°	6884.3
7°	6592.3
8°	6258.0
9°	5892.4
10°	5484.4
11°	5014.1
12°	4472.6
13°	3906.2
14°	3298.7
15°	2697.3
17.5°	1537.0
20°	862.1
22.5°	520.2
25°	330.6
27.5°	203.4
30°	118.5
32.5°	62.4
35°	32.4
37.5°	21.2
40°	13.7
42.5°	8.7
45°	5.0
47.5°	3.7
50°	3.7
52.5°	3.7
55°	2.5
57.5°	2.5
60°	2.5
62.5°	2.5
65°	2.5
67.5°	2.5
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1270121
CATALOG NUMBER: P3A17R259740DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)