

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267962

Luminaire Tested: P3A17R609735DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267962  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R609735DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 485.0 lumens  
Efficiency: N/A  
Efficacy: 22.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267962  
CATALOG NUMBER: P3A17R609735DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1267962  
 CATALOG NUMBER: P3A17R609735DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86090
5°	85120
10°	82185
15°	77639
20°	71570
25°	64794
30°	57528
35°	49175
40°	39102
45°	27569
50°	16477
55°	8334
60°	7982
65°	7316
70°	6796
75°	6524
80°	5935
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27569 cd/sqm



TEST NUMBER: P1267962

CATALOG NUMBER: P3A17R609735DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.3	7.5
10°-20°	95.6	19.7
20°-30°	122.7	25.3
30°-40°	113.8	23.5
40°-50°	69.3	14.3
50°-60°	23.1	4.8
60°-70°	14.0	2.9
70°-80°	7.9	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.6	52.5
0°-40°	368.4	76.0
0°-60°	460.8	95.0
0°-90°	485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	485.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	393	
5°	387	36
15°	342	96
25°	268	123
35°	184	114
45°	89	69
55°	22	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1267962  
CATALOG NUMBER: P3A17R609735DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	392.6
2.5°	390.9
5°	386.7
7.5°	379.1
10°	369.1
12.5°	356.7
15°	342.0
17.5°	324.9
20°	306.7
22.5°	287.3
25°	267.8
27.5°	247.8
30°	227.2
32.5°	206.6
35°	183.7
37.5°	159.5
40°	136.6
42.5°	112.4
45°	88.9
47.5°	68.9
50°	48.3
52.5°	28.8
55°	21.8
57.5°	20.0
60°	18.2
62.5°	15.9
65°	14.1
67.5°	12.4
70°	10.6
72.5°	8.8
75°	7.7
77.5°	5.9
80°	4.7
82.5°	2.9
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)